

Separate Sheet

Product Specifications of the R-Car W2R

Product name (product no.)	R-Car W2R (R7S720004)
Applicable standard	IEEE 802.11p
Frequency band	5.9 GHz
Power supply voltage	3.3 V (I/O), 1.2 V (core)
CPU core	32-bit (operating frequency: 160 MHz)
On-chip memory	RAM: 128 KB, ROM: 32 KB
Host interface	SDIO
Memory interface	I ² C
Package	176-pin plastic FPBGA (10 mm × 10 mm)
Operating temperature range	Ta = -40 to +85 °C (JEDEC JESD 51-9), Tj = -40 to +125°C

All registered trademarks or trademarks are the property of their respective owners.