

**Separate Sheet**

**Product Specifications of the RAA305315GBM**

Product no.	RAA305315GBM
Model name	RAA305315GBM
Supply voltage	VDD: 1.7 V - 3.3 V VCC: 2.7 V - 3.3 V VM: 2.7 V - 3.3 V
Operating temperature	-20°C - +75°C
CPU core	32-bit RISC CPU
DSP	GREEN-DSP (32-bit) servo control
Memory	CPU: Code flash + SRAM /DSP: SRAM
OIS/AF driver	OIS: 2 channels (ISX, ISY)/ AF: 1 channel
HALL signal input	3 channels (8-bit DAC/ Constant Current Bias/ Gain Amp)
ADC input	6 channels
SPI	1 channel
I2C	1 channel
16-bit timer	4 channels

###

All registered trademarks or trademarks are the property of their respective owners