

Separate Sheet

Product specifications of the RAA462113FYL

Part name	RAA462113FYL
Sensor	Optical format 1/1.9 inch
	1.85um ² BSI pixel
	Effective area 3872 (H) x 2192 (V)
Output I/F	SLVS (891Mbps/lane), MIPI CSI-2
Supply voltage (Typ.)	2.8V/1.8V/1.2V
Package	144-pin LGA
Read Mode	UHD Active area 3840 x 2160, max60fps, 12-bit
	HD Active area 1920 x1 080, max60fps, 12-bit

###

(Remarks) All names of products or services mentioned in this press release are trademarks or registered trademarks of their respective owners.