

Application Note

DA9210 Linux Mainline Device Driver

AN-SW-101

Abstract

Description of build and loading instructions, and a list of features provided by the DA9210 Linux Mainline device driver.

DA9210 Linux Mainline Device Driver

Terms and Definitions

I ² C	Inter-Integrated Circuit (bus)
IRQ	Interrupt Request (line)

References

- [1] DA9210, Datasheet, Dialog Semiconductor.

Introduction

The purpose of this document is to describe the release of the DA9210 PMIC Linux Mainline device driver package. It will cover the following:

- build and loading instructions and;
- a description of the features provided by this driver.

These instructions cover the device driver content and the device tree data where appropriate. It is expected that anyone reading this document has a good understanding of Linux and the Linux kernel.

Dependencies

This release depends upon a clean, correctly compiled and working Linux kernel linux-stable tree, tag v3.12 or later. This Linux kernel is not provided by Dialog Semiconductor. The kernel is provided by The Linux Kernel Archives (<https://www.kernel.org/>). The tag v3.12 (or later) can be checked out from the Linux kernel linux-stable repository.

System Requirements

- Linux kernel source from the repository linux-stable, tagged as v3.12 or later.
- Dialog Semiconductor DA9210.

Features

The following features are supported by the DA9210 PMIC Linux device driver.

- Platform data support for the device
- Device tree support for the device
- I²C communication support
- IRQ support
- Bucks
 - Activate and deactivate regulator (on/off)
 - Specify voltage settings for buck
 - Define the current limits for buck

Installation

All DA9210 device driver sources come as part of the Linux kernel. In addition to this, further steps are required to fully integrate the device driver into the kernel tree.

DA9210 Linux Mainline Device Driver

- Information to add devices into the host platform.
- Configuration of the Linux build system.

Device Tree Bindings

Add bindings for the DA9210 into the device tree schema for the target platform. The DA9210 device driver uses common frameworks and interfaces exported by the Linux kernel. The support for device tree and DA9210 bindings can be found in the kernel documentation.

```
./Documentation/devicetree/bindings/regulator/da9210.txt
```

Platform Data

Update machine code in arch/arm/mach-<machine> to add platform specific code for the DA9210 driver.

Compilation

The instructions are provided in the kernel source tree. For further instructions, see the top level README file in the Linux kernel.

Interfaces

Device Driver Interface

This section describes the interfaces supported by the DA9210 PMIC driver.

- I²C: The driver supports the I²C interface for control of the device.
- Sysfs Interface: The driver natively supports the kernel's sysfs framework. Each component provides a set of file access points under the kernel directory /sys.

Device Tree Interface

The support for device tree can be found in the Linux kernel binding documentation. DT bindings for the DA9210 are given in the device tree specification files.

Revision History

Revision	Date	Description
000	22-Nov-2013	Initial Application Note
1v0	10-Aug-2016	New format document. Additions for IRQ support. Additions for device tree support.

DA9210 Linux Mainline Device Driver

Status Definitions

Status	Definition
DRAFT	The content of this document is under review and subject to formal approval, which may result in modifications or additions.
APPROVED or unmarked	The content of this document has been approved for publication.

Disclaimer

Information in this document is believed to be accurate and reliable. However, Dialog Semiconductor does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information. Dialog Semiconductor furthermore takes no responsibility whatsoever for the content in this document if provided by any information source outside of Dialog Semiconductor.

Dialog Semiconductor reserves the right to change without notice the information published in this document, including without limitation the specification and the design of the related semiconductor products, software and applications.

Applications, software, and semiconductor products described in this document are for illustrative purposes only. Dialog Semiconductor makes no representation or warranty that such applications, software and semiconductor products will be suitable for the specified use without further testing or modification. Unless otherwise agreed in writing, such testing or modification is the sole responsibility of the customer and Dialog Semiconductor excludes all liability in this respect.

Customer notes that nothing in this document may be construed as a license for customer to use the Dialog Semiconductor products, software and applications referred to in this document. Such license must be separately sought by customer with Dialog Semiconductor.

All use of Dialog Semiconductor products, software and applications referred to in this document are subject to Dialog Semiconductor's [Standard Terms and Conditions of Sale](http://www.dialog-semiconductor.com), available on the company website (www.dialog-semiconductor.com) unless otherwise stated.

Dialog and the Dialog logo are trademarks of Dialog Semiconductor plc or its subsidiaries. All other product or service names are the property of their respective owners.

© 2016 Dialog Semiconductor. All rights reserved.

Contacting Dialog Semiconductor

United Kingdom (Headquarters)

Dialog Semiconductor (UK) LTD
Phone: +44 1793 757700

Germany

Dialog Semiconductor GmbH
Phone: +49 7021 805-0

The Netherlands

Dialog Semiconductor B.V.
Phone: +31 73 640 8822

Email:

enquiry@diasemi.com

North America

Dialog Semiconductor Inc.
Phone: +1 408 845 8500

Japan

Dialog Semiconductor K. K.
Phone: +81 3 5425 4567

Taiwan

Dialog Semiconductor Taiwan
Phone: +886 281 786 222

Web site:

www.dialog-semiconductor.com

Singapore

Dialog Semiconductor Singapore
Phone: +65 64 8499 29

Hong Kong

Dialog Semiconductor Hong Kong
Phone: +852 3769 5200

Korea

Dialog Semiconductor Korea
Phone: +82 2 3469 8200

China (Shenzhen)

Dialog Semiconductor China
Phone: +86 755 2981 3669

China (Shanghai)

Dialog Semiconductor China
Phone: +86 21 5424 9058

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.