




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PTA21CM	PLQP0048JA-A	FP-48F / FP-48FV
	PLQP0064KC-A	FP-64E / FP-64EV

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	17.9
	Z_L	18.4
	e_w	25
	e_L	31
	S_w	55
Thickness (mm)	H_1	7.6
	H_2	2.5
Number of cells	N_w	5
	N_L	10
Maximum storage No. IC/Tray		50
Maximum storage No. IC/Inner box		500
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack