




# CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT725B	PRQJ0044DB-A	CP-44 / CP-44V

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	$Z_W$	17.9
	$Z_L$	18.4
	$e_w$	25
	$e_L$	31
	$S_w$	25
Thickness (mm)	$H_1$	9.5
	$H_2$	2.5
Number of cells	$N_W$	5
	$N_L$	10
Maximum storage No. IC/Tray		50
Maximum storage No. IC/Inner box		500
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack/Non dry pack