




CUSTOM TRAY

Tray Code	RENESAS Code	Previous Code
PT826C	PRQJ0068DB-A	CP-68 / CP-68V

Unit:mm



The pin1 is located in the hatching portion



Position dimension of cells (mm)	Z_W	21.4
	Z_L	25.9
	e_w	31
	e_L	33
	S_w	55
Thickness (mm)	H_1	7.6
	H_2	2.5
Number of cells	N_W	4
	N_L	9
Maximum storage No. IC/Tray		36
Maximum storage No. IC/Inner box		324
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack/Non dry pack