


# JEDEC TRAY

Tray Code	RENESAS Code	Previous Code
PTA55C	PRQP0044GC-A	FP-44A / FP-44AV
	PRQP0064GB-A	FP-64A / FP-64AV
	PRQP0064GC-A	FP-64H / FP-64HV
	PRQP0080JB-A	FP-80A / FP-80AV
	PRQP0080JD-A	FP-80Q / FP-80QV

Unit:mm



The pin1 is located in the hatching portion

Position dimension of cells (mm)	$Z_w$	15.45
	$Z_L$	17.75
	$e_w$	21
	$e_L$	21.5
Thickness (mm)	$H_1$	7.62
Number of cells	$N_w$	6
	$N_L$	14
Maximum storage No. IC/Tray		84
Maximum storage No. IC/Inner box		672
Material		Carbon PPE
Surface resistance		Less than $1 \times 10^{11} \Omega / \square$
Heat resistant temperature		125°C24h
Packing form		Dry pack