




<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>MASS (Typ.) [g]</b>
P-FBGA1022-29×29-0.80	PRBG1022GA-B	3.2



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
D	28.8	29.0	29.2
E	28.8	29.0	29.2
A	(2.1)	(2.3)	2.5
A <sub>1</sub>	0.35	0.40	0.45
e	—	0.8	—
b	0.45	0.50	0.55
x <sub>1</sub>	—	—	0.20
x <sub>2</sub>	—	—	0.08
y	—	—	0.15
y <sub>1</sub>	—	—	0.20