

January 31, 2011

Product Specifications of the PS7901D-1A Device

- Ultra-compact package
- Low output capacitance: 0.75 pF (typ.), low on-resistance: 12 Ω (typ.)
- Low leakage current: 30 pA (typ.)
- Low input LED current: $I_{Fon} = 4$ mA (max.)
- High I/O insulation voltage tolerance: $BV = 500$ V r.m.s.
- Embossed tape packaging: PS7901D-1A-F3 (3,500 pcs/reel)
- Lead-free
- Applications: IC testers, measuring equipment, factory automation equipment and office equipment