

Separate Sheet

Product Specifications of the R-Car V3H

- Arm® Cortex®-A53 (1000MHz) CPU × 4
- Dual Lockstep Arm Cortex-R7 (800MHz) CPU × 2
- Memory controller for LPDDR4-3200 with 32 bits × 1 channel
- Image recognition engine (IMP-X5-V3H)
- Dedicated hardware accelerator for CNN, Dense Optical Flow, Stereovision and Object Classification
- Dual Image Signal Processor (ISP)
- Video Output (4 lanes × 1 channel LVDS, 1 channel digital)
- Video Input (4 lanes × 2 channels MIPI-CSI2, 2 channels digital)
- CAN-FD interface 2 channels
- FlexRay interface 1 channel
- Gigabit Ethernet and AVB Ethernet 1 channel
- PCI Express interface 1 channel

###

(Remarks) Arm and Cortex are registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. All rights reserved. All other registered trademarks or trademarks are the property of their respective owners.