


SYMBOLS	LIMITS		INCHES	
	MIN	MAX	MIN	MAX
A	.160	.185		
A1	.015	.035		
b	.015	.020		
b1	.050	.065		
C	.008	.012		
D	1.240	1.260		
E	.600	.620		
E1	.530	.550		
e	.090	.110		
eA	.610	.670		
L	.120	.150		
∠	0°	15°		
N	24			
Q1	.060	.080		
S	.060	.080		

JEDEC	EXCEPTIONS
STD-MO-015 (AA)	A1=.020-.070 b=.016-.020

TOLERANCES UNLESS OTHERWISE SPECIFIED	
FRAC	DEC ANGLES
± - ± - ± -	± - ± - ± -
APPROVALS	DATE
DRAWN <i>AA</i>	7/88
CHECKED	
<i>MF</i>	<i>8/88</i>



Integrated Device Technology, Inc.
 3236 Scott Blvd., Santa Clara, CA 95051
 (408) 727-6116 TWX: 910-338-2070

24 LD P-DIP MKT DWG (600 MIL)			
SCALE	SIZE	DRAWING NO.	REV
N/A	A	PSC-4010	03
DO NOT SCALE DRAWING			SHEET 2 OF 2