


- NOTE :**
1. DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS 0.25 MM. PER SIDE AND MAXIMUM PLASTIC BODY SIZE DIMENSIONS INCLUDING MOLD MISMATCH.
  2. LEAD WIDTH DIMENSION DOES NOT INCLUDE DAMBER PROTRUSION.
  3. THIS PART REFERENCE JEDEC DRAWING NO. MS-026 VARIATION ACD.
  4. FOOT LENGTH IS MEASUREMENT AT GAGE PLANE 0.25 MM ABOVE SEATING PLANE.
  5. LEAD SPAN/STAND OFF HEIGHT/COPLANARITY ARE CONSIDERED AS SPECIAL CHARACTERISTIC(S)
  6. COO & CAVITY ID ARE INCLUDED IN PIN#1 IDENTIFICATION.
  7. CONTROLLING DIMENSION IN MM.



EPAD 7.5 mm SQ

Package Revision History		
Date Created	Rev No.	Description
4/29/21	00	Initial Release