







REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	6/16/16	J.H




SYMBOL	PITCH VARIATION			NOTE
	MIN.	NOM.	MAX.	
leT	0.50 BSC			
leR	0.65 BSC			
N	132			3
NDa	18			3
NDb	15			3
NEa	18			3
NEb	15			3
La	0.30	0.40	0.50	
Lb	0.30	0.40	0.50	
b	0.17	0.22	0.27	4
D2	4.15	4.45	4.60	
E2	4.15	4.45	4.60	



- NOTE:
1. ALL DIMENSION ARE IN mm, ANGLES IN DEGREES
  2. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS. COPLANARITY SHALL NOT EXCEED 0.08 mm
  3. WARPAGE SHALL NOT EXCEED 0.10.
  4. PACKAGE LENGTH/PACKAGE WIDTH ARE CONSIDERD AS SPECIAL CHARACTERIS (S)

TOLERANCES UNLESS SPECIFIED		 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 <a href="http://www.IDT.com">www.IDT.com</a>
DECIMAL	ANGULAR	
X±		
XX±		
XXX±		
APPROVALS	DATE	TITLE
DRAWN <i>JP</i>	07/10/07	NQ/NQG132 PACKAGE OUTLINE
CHECKED		10.0 x 10.0 mm BODY, EPAD 4.45mm SQ. 0.50mm Pitch Dual-Row QFN
	SIZE	DRAWING No.
	C	PSC-4327-01
		REV
		00
DO NOT SCALE DRAWING		SHEET 1 OF 2


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
00	INITIAL RELEASE	6/16/16	J.H



RECOMMENDED LAND PATTERN

NOTE:

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. TOP DOWN VIEW, AS VIEWED ON PCB.
3. COMPONENT OUTLINE SHOWS FOR REFERENCE IN GREEN.
4. LAND PATTERN IN BLUE. NSMD PATTERN ASSUMED.
5. LAND PATTERN RECOMMENDATION PER IPC-7351B GENERIC REQUIREMENT FOR SURFACE MOUNT DESIGN AND LAND PATTERN.

TOLERANCES UNLESS SPECIFIED		 <b>IDT™</b> 6024 Silver Creek Valley Road San Jose, CA 95138 PHONE: (408) 284-8200 FAX: (408) 284-8591 <a href="http://www.IDT.com">www.IDT.com</a>	
DECIMAL	ANGULAR		
X±		<b>TITLE</b> NQ/NQG132 PACKAGE OUTLINE <b>10.0 x 10.0 mm BODY, EPAD 4.45mm SQ.</b> <b>0.50mm Pitch Dual-Row QFN</b>	
XX±			
XXX±			
APPROVALS	DATE	DRAWN <i>BP</i> 07/10/07	
CHECKED			
SIZE	DRAWING No.	REV	
C	PSC-4327-01	00	
DO NOT SCALE DRAWING		SHEET 2 OF 2	