


<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>Previous Code</b>	<b>MASS (Typ) [g]</b>
P-DBGA112-10.7x12.3-0.80	WRBG0112GB-A	—	0.42

Unit: mm



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	12.20	12.30	12.40
E	10.60	10.70	10.80
A	—	—	2.20
A1	0.37	0.41	0.45
e	—	0.80	—
b	0.45	0.50	0.55
X1	—	—	0.15
X2	—	—	0.08
y	—	—	0.10
y1	—	—	0.20
n	—	112	—
Z <sub>D</sub>	—	1.35	—
Z <sub>E</sub>	—	2.15	—