



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	21.0	—
E	—	21.0	—
v	—	—	0.20
w	—	—	0.30
A	—	—	2.10
A ₁	0.36	0.46	0.56
e	—	1.00	—
b	0.53	0.63	0.73
x	—	—	0.10
y	—	—	0.15
y ₁	—	—	0.35
S _D	—	—	—
S _E	—	—	—
Z _D	—	1.00	—
Z _E	—	1.00	—