


<b>JEITA Package Code</b>	<b>RENESAS Code</b>	<b>MASS (Typ) [g]</b>
P-LFBGA400-17x17-0.80	PLBG0400GB-A	0.88



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
D	16.90	17.00	17.10
E	16.90	17.00	17.10
A	—	—	1.70
A1	0.35	0.40	0.45
$e$	—	0.80	—
b	0.45	0.50	0.55
$x_1$	—	—	0.15
$x_2$	—	—	0.08
y	—	—	0.10
$y_1$	—	—	0.20
n	—	400	—
$Z_D$	—	0.90	—
$Z_E$	—	0.90	—