




729-PIN PLASTIC BGA (FLIP CHIP TYPE) (29x29)



DETAIL OF (A) PART



ITEM	MILLIMETERS
D	29.00±0.10
D1	10.94
E	29.00±0.10
E1	10.94
w	0.15
e	1.00
A	2.31±0.30
A1	0.45±0.10
A2	1.00±0.10
b	0.60±0.10
x	0.10
y	0.20
y1	0.30
ZD	1.50
ZE	1.50

P729S7-100-C7