





JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-70	PTSP0003ZA-A	CMPAK / CMPAKV	0.006



A-A Section

Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
A	0.8	—	1.1
A ₁	0	—	0.1
A ₂	0.8	0.9	1.0
A ₃	—	0.25	—
b	0.25	0.3	0.4
c	0.1	0.16	0.26
D	1.8	2.0	2.2
E	1.15	1.25	1.35
e	—	0.65	—
H _E	1.8	2.1	2.4
L	0.3	—	0.7
L ₁	0.1	—	0.5
L _P	0.2	—	0.6
x	—	—	0.05
Q	—	0.2	—