



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	21.0	—
E	—	21.0	—
v	—	—	0.15
w	—	—	0.20
A	—	—	1.9
A ₁	0.35	0.40	0.45
e	—	0.80	—
b	0.45	0.50	0.55
x	—	—	0.08
y	—	—	0.10
y ₁	—	—	0.20
S _D	—	—	—
S _E	—	—	—
Z _D	—	0.9	—
Z _E	—	0.9	—