





JEITA Package Code
P-FQFP240-32x32-0.50

RENESAS Code
PRQP0240KA-A

Previous Code
240P6Y-A

MASS[Typ.]
8.1g



NOTE)
1. DIMENSIONS $*1$ " AND $*2$ "
DO NOT INCLUDE MOLD FLASH.
2. DIMENSION $*3$ " DOES NOT
INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	31.9	32.0	32.1
E	31.9	32.0	32.1
A_2	—	3.6	—
H_D	34.4	34.6	34.8
H_E	34.4	34.6	34.8
A_1	0.25	0.35	0.45
b_p	0.15	0.2	0.3
c	0.13	0.15	0.2
θ	0°	—	10°
e	0.4	0.5	0.6
y	—	—	0.10
Z_D	—	1.25	—
Z_E	—	1.25	—
L	0.3	0.5	0.7