



899-PIN PLASTIC BGA (FLIP CHIP TYPE) (40x40)



detail of (A) part



ITEM	MILLIMETERS
D	40.00±0.10
RD	39.10±0.10
E	40.00±0.10
RE	39.10±0.10
w	0.20
e	1.27
SD	0.635
SE	0.635
A	3.06±0.40
A1	0.60±0.10
A2	2.46
b	0.75±0.15
x	0.10
y	0.20
y1	0.30
ZD	1.59
ZE	1.59