





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-HVQFN40-6x6-0.50	PVQN0040KC-A	—	0.10g

NOTE)
b1,c1: DIMENSION BEFORE PLATING



アウターリード部図
Outer lead detail

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	6.00	—
E	—	6.00	—
A	—	—	0.95
A ₁	0.005	—	—
b	0.17	0.22	0.27
b ₁	—	0.20	—
e	—	0.50	—
L _p	0.40	0.50	0.60
x	—	—	—
y	—	—	0.05
y ₁	—	—	—
t	—	—	—
H _D	—	6.20	—
H _E	—	6.20	—
Z _D	—	0.75	—
Z _E	—	0.75	—
c	0.17	0.22	0.27
c ₁	—	0.20	—