

JEITA Package Code

RENESAS Code

Previous Code





MASS[Typ.]

P-HWQFN40-5x5-0.40

PWQN0040LD-A

40PJR-A

0.05g



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
$D$	4.9	5.0	5.1
$E$	4.9	5.0	5.1
$A_2$	—	0.75	—
$A$	—	—	0.8
$A_1$	0	0	0.05
$b_p$	0.15	0.2	0.25
$e$	—	0.4	—
$L_p$	0.2	0.3	0.4
$x$	—	—	0.05
$y$	—	—	0.05
$Z_D$	—	0.7	—
$Z_E$	—	0.7	—
$D_2$	—	3.0	—
$E_1$	—	3.0	—