



## 40 PIN PLASTIC FBGA (6x10.5)



ITEM	MILLIMETERS
A	10.65±0.15
B	6.15±0.15
C	1.2
D	1.575
E	0.75
F	0.75
G	0.22±0.07
I	0.9
J	1.12±0.15
K	0.10
L	0.425±0.07
M	0.08
N1	1.125
N2	0.75
P	C0.6
R	25°

P40F3-75-BF1