



# 52 PIN PLASTIC FBGA (7x11.5)



| ITEM | MILLIMETERS |
|------|-------------|
| A    | 11.65±0.15  |
| B    | 7.15±0.15   |
| C    | 1.575       |
| D    | 1.025       |
| E    | 0.8         |
| F    | 0.8         |
| G    | 0.22±0.07   |
| I    | 0.9         |
| J    | 1.12±0.15   |
| K    | 0.10        |
| L    | 0.425±0.07  |
| M    | 0.08        |
| N    | 1.2         |
| P    | C0.8        |
| R    | 25°         |