




# 64-PIN PLASTIC FBGA (8x8)



ITEM	MILLIMETERS
A	8.00±0.10
B	7.40
C	7.40
D	8.00±0.10
E	1.20
F	0.8 (T.P.)
G	0.35±0.1
H	0.36
I	0.96
J	1.31±0.15
K	0.10
L	$\phi 0.50^{+0.05}_{-0.10}$
M	0.08
P	C1.0
Q	R0.3
R	25°
W	0.20
Y1	0.20

S64F1-80-CA1-1