



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	6.92	7.00	7.08
E	6.92	7.00	7.08
v	—	—	—
w	—	—	0.15
A	1.13	1.23	1.33
A ₁	0.28	0.33	0.38
e	—	0.65	—
b	0.35	0.40	0.45
x	—	—	0.05
y	—	—	0.08
y ₁	—	—	—
S _D	—	—	—
S _E	—	—	—
Z _D	—	0.575	—
Z _E	—	0.575	—