

外形図 Outline drawing
 Renesasコード PLQP0144LC-B




RDK-G-001628

1/1

ルネサスエレクトロニクス株式会社
 Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-HLFQFP144-16x16-0.40	PLQP0144LC-B	0.90

UNIT:MM



Terminal Cross Section

Note)

1. DIMENSIONS "*1" and "2" DO NOT INCLUDE MOLD FLASH.
2. DIMENSION "*3" DOES NOT INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.60
A ₁	0.05	—	0.15
A ₂	—	1.40	—
D	17.80	18.00	18.20
D ₁	15.80	16.00	16.20
E	17.80	18.00	18.20
E ₁	15.80	16.00	16.20
N	—	144	—
e	—	0.40	—
b	0.13	0.18	0.23
b ₁	0.13	0.16	0.19
c	0.09	—	0.20
c ₁	0.09	—	0.16
θ	0°	—	7°
L	0.45	0.60	0.75
L ₁	—	1.00	—
D2	—	6.70	—
E2	—	6.70	—
ccc	—	—	0.08
ddd	—	—	0.07