



外形図 Outline drawing  
 Renesasコード PLQP0208KD-A

RDK-G-001830

1/1

ルネサスエレクトロニクス株式会社  
 Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-LFQFP208-28x28-0.50	PLQP0208KD-A	2.6g



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.70
A <sub>1</sub>	0.05	—	0.15
A <sub>2</sub>	1.35	1.40	1.45
D	30.00 BSC.		
D <sub>1</sub>	28.00 BSC.		
E	30.00 BSC.		
E <sub>1</sub>	28.00 BSC.		
N	—	208	—
e	0.50 BSC.		
b	0.17	0.22	0.27
c	0.095	—	0.195
θ	0°	3.5°	8°
L <sub>1</sub>	1.00 REF.		
aaa	—	—	0.20
bbb	—	—	0.20
ccc	—	—	0.08
ddd	—	—	0.08