




外形図 Outline drawing
 Renesasコード PLQP0100JE-A

RDK-G-001675

1/1

ルネサスエレクトロニクス株式会社
 Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-LQFP100-14x20-0.65	PLQP0100JE-A	0.98



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.60
A ₁	0.05	—	0.15
A ₂	1.35	1.40	1.45
D	—	22.00	—
D ₁	—	20.00	—
E	—	16.00	—
E ₁	—	14.00	—
N	—	100	—
e	—	0.65	—
b	0.22	0.32	0.38
c	0.09	—	0.20
θ	0°	3.5°	7°
L	0.45	0.60	0.75
L ₁	—	1.00	—
aaa	—	—	0.20
bbb	—	—	0.20
ccc	—	—	0.10
ddd	—	—	0.13