


80-PIN PLASTIC LQFP (14x14)



NOTE

Each lead centerline is located within 0.13 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	16.0±0.2
B	14.0±0.1
C	14.0±0.1
D	16.0±0.2
F	0.825
G	0.825
H	0.30±0.10
I	0.13
J	0.65 (T.P.)
K	1.0±0.2
L	0.5±0.2
M	0.125 ^{+0.10} _{-0.05}
N	0.10
P	1.4±0.1
Q	0.125±0.075
R	3° ^{+7°} _{-3°}
S	1.7 MAX.

S80GC-65-7ET-3