






JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-61AA	PLSP0004ZA-A	MPAK-4 / MPAK-4V	0.013



Reference Symbol	Dimensions in millimeters		
	Min	Nom	Max
A	1.0	—	1.3
A <sub>1</sub>	0	—	0.1
A <sub>2</sub>	1.0	1.1	1.2
A <sub>3</sub>	—	0.25	—
b	0.35	0.4	0.5
b <sub>1</sub>	0.55	0.6	0.7
c	0.1	0.16	0.26
D	2.7	—	3.1
E	1.35	1.5	1.65
e	—	0.95	—
e <sub>2</sub>	—	0.85	—
H <sub>E</sub>	2.2	2.8	3.0
L	0.35	—	0.75
L <sub>1</sub>	0.15	—	0.55
L <sub>P</sub>	0.25	—	0.65
x	—	—	0.05
y	—	—	0.05
Q	—	0.3	—