





JEITA Package Code	RENASAS Code	Previous Code	MASS[Typ.]
P-QFJ68-24.2x24.2-1.27	PRQJ0068DB-A	CP-68/CP-68V	4.2g



Terminal cross section



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	24.20	—
E	—	24.20	—
$H_D$	25.02	25.15	25.27
$H_E$	25.02	25.15	25.27
$A_1$	—	0.90	—
A	4.20	4.40	4.60
b	0.32	0.42	0.52
$b_1$	—	0.38	—
$b_2$	—	0.75	—
c	—	—	—
$c_1$	—	—	—
$e$	—	1.27	—
x	—	—	0.20
y	—	—	0.10
L	2.40	2.55	2.70
$e_{1D}$	22.62	23.12	23.62
$e_{1E}$	22.62	23.12	23.62
$Z_D$	—	1.94	—
$Z_E$	—	1.94	—