





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-QFJ84-29.28x29.28-1.27	PRQJ0084DB-A	CP-84/CP-84V	6.4g



Terminal cross section



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	29.28	—
E	—	29.28	—
H <sub>D</sub>	30.10	30.23	30.35
H <sub>E</sub>	30.10	30.23	30.35
A <sub>1</sub>	—	0.90	—
A	4.20	4.40	4.60
b	0.32	0.42	0.52
b <sub>1</sub>	—	0.38	—
b <sub>2</sub>	—	0.75	—
c	—	—	—
c <sub>1</sub>	—	—	—
e	—	1.27	—
x	—	—	0.20
y	—	—	0.10
L	2.40	2.55	2.70
e <sub>1D</sub>	27.70	28.20	28.70
e <sub>1E</sub>	27.70	28.20	28.70
Z <sub>D</sub>	—	1.94	—
Z <sub>E</sub>	—	1.94	—