



54 PIN PLASTIC QFP (9.5)



detail of lead end



P54G-65-R-2

NOTE

Each lead centerline is located within 0.15 mm (0.006 inch) of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS	INCHES
A	13.9±0.4	0.547±0.016
B	9.5±0.2	0.374±0.008
C	9.5±0.2	0.374±0.008
D	13.9±0.4	0.547±0.016
F	0.5	0.020
G	0.85	0.033
H	0.30±0.10	0.012 ^{+0.004} _{-0.005}
I	0.15	0.006
J	0.65 (T.P.)	0.026 (T.P.)
K	2.2±0.2	0.079 ^{+0.008} _{-0.009}
L	0.9±0.2	0.047 ^{+0.009} _{-0.008}
M	0.15 ^{+0.10} _{-0.05}	0.006 ^{+0.004} _{-0.003}
N	0.15	0.006
P	1.5±0.1	0.059±0.004
Q	0.1±0.1	0.004±0.004
S	1.8 MAX.	0.071 MAX.