

JEITA Package Code

RENESAS Code

Previous Code




MASS[Typ.]

P-QFP80-14x20-0.80


PRQP0080GD-A

FP-80/FP-80V

1.8g



Terminal cross section



Detail F

NOTE)

1. DIMENSIONS**1"AND**2"
DO NOT INCLUDE MOLD FLASH
2. DIMENSION**3"DOES NOT
INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	20	—
E	—	14	—
A ₂	—	2.70	—
H _D	25.2	25.6	26.0
H _E	19.2	19.6	20.0
A	—	—	3.10
A ₁	0	—	—
b _p	0.29	0.37	0.45
b ₁	—	0.35	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	10°
e	0.65	0.8	0.95
x	—	—	—
y	—	—	—
Z _D	—	0.8	—
Z _E	—	1.0	—
L	1.4	1.7	2.0
L ₁	—	2.8	—