




NOTE)

1. DIMENSIONS\*\*1"AND\*\*2"  
DO NOT INCLUDE MOLD FLASH
2. DIMENSION\*\*3"DOES NOT  
INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14	—
E	—	14	—
A <sub>2</sub>	—	2.70	—
H <sub>D</sub>	17.0	17.2	17.4
H <sub>E</sub>	17.0	17.2	17.4
A	—	—	3.05
A <sub>1</sub>	0.00	0.10	0.25
b <sub>p</sub>	0.24	0.32	0.40
b <sub>1</sub>	—	0.30	—
c	0.12	0.17	0.22
c <sub>1</sub>	—	0.15	—
θ	0°	—	8°
⌀	—	0.65	—
x	—	—	0.12
y	—	—	0.10
Z <sub>D</sub>	—	0.83	—
Z <sub>E</sub>	—	0.83	—
L	0.6	0.8	1.0
L <sub>1</sub>	—	1.6	—