



## NOTE)

1. DIMENSIONS<sup>\*\*1</sup> (Nom)<sup>\*\*AND</sup>\*2<sup>\*\*</sup> DO NOT INCLUDE MOLD FLASH.
2. DIMENSION<sup>\*\*3</sup> DOES NOT INCLUDE TRIM OFFSET.



Terminal cross section



Detail F

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	20.45	20.95
E	—	11.30	—
A <sub>2</sub>	—	—	—
A <sub>1</sub>	0.05	0.15	0.27
A	—	—	3.00
b <sub>p</sub>	0.32	0.40	0.48
b <sub>1</sub>	—	0.38	—
c	0.17	0.22	0.27
c <sub>1</sub>	—	0.20	—
θ	0°	—	8°
H <sub>E</sub>	13.84	14.14	14.44
e	—	1.27	—
x	—	—	0.15
y	—	—	0.10
Z	—	—	1.00
L	0.60	0.80	1.00
L <sub>1</sub>	—	1.42	—