


外形図 Outline drawing  
 Renesasコード PRSP0008DV-A

RDK-G-001818 1/1

ルネサスエレクトロニクス株式会社  
 Renesas Electronics Corporation

JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-SOP08-3.90×4.90-1.27	PRSP0008DV-A	0.08



Reference Symbol	Dimension in Millimeters		
	Min.	Nom.	Max.
A	—	—	1.75
A1	0.10	—	0.25
A2	1.25	—	—
b	0.31	—	0.51
c	0.10	—	0.25
D	—	4.90	—
E	—	6.00	—
E1	—	3.90	—
e	—	1.27	—
L	0.40	—	1.27
theta	0	—	8
aaa	—	—	0.10
bbb	—	—	0.20
ccc	—	—	0.10
ddd	—	—	0.25
eee	—	—	0.10

NOTES:  
 1. JEDEC OUTLINE : MS-012 AA  
 2. DIMENSIONS "D" DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.  
 MOLD FLASH, PROTRUSIONS AND GATE BURRS SHALL NOT EXCEED 0.15mm. PER SIDE.  
 3. DIMENSIONS "E1" DOES NOT INCLUDE INTER-LEAD FLASH, OR PROTRUSIONS.  
 INTER-LEAD FLASH AND PROTRUSIONS SHALL NOT EXCEED 0.25mm PER SIDE.