





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-SSOP42-8.4x17.5-0.80	PRSP0042GC-A	42P2L-A	0.7g



Detail F

NOTE)
 1. DIMENSIONS $*1*$ AND $*2*$
 DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION $*3*$ DOES NOT
 INCLUDE TRIM OFFSET.

Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	17.3	17.5	17.7
E	8.2	8.4	8.6
A_2	—	2	—
H_E	11.63	11.93	12.23
A	—	—	2.4
A_1	0.05	—	—
b_p	0.25	0.3	0.4
c	0.13	0.15	0.2
θ	0°	—	10°
\ominus	—	0.8	—
x	—	—	0.16
y	—	—	0.15
Z_D	—	0.75	—
L	0.3	0.5	0.7