





# 420-PIN TAPE BGA (HEAT SPREADER TYPE) (35x35)



⊕	$\phi M$	M	S	A	B
	$\phi P$	M	S		



ITEM	MILLIMETERS
A	35.00±0.20
A1	20.50 MAX.
A2	20.50 MAX.
B	34.60±0.15
C	34.60±0.15
D	35.00±0.20
E	1.625
F	1.27 (T.P.)
G	0.60±0.10
H	0.80
J	1.40 <sup>+0.30</sup> <sub>-0.20</sub>
K	0.15
L	∅0.75±0.15
M	0.30
N	0.25 MIN.
P	0.10
Q	3.0
R	2.0
S	2.0
T	3.0
W	20.19
X	20.19
Y	C 0.40
Z	0.20