


69-PIN TAPE FBGA (11x8)



ITEM	MILLIMETERS
D	8.0±0.1
E	11.0±0.1
w	0.2
e	0.8
A	1.12±0.10
A1	0.27±0.05
A2	0.85
b	0.45±0.05
x	0.08
y	0.1
y1	0.1
ZD	0.4
ZE	1.1

P69F9-80-CD2