


60-PIN TAPE FBGA (14.76x7.83)



ITEM	MILLIMETERS
D	7.83±0.10
E	14.76±0.10
v	0.15
w	0.2
A	0.96±0.10
A1	0.40±0.05
A4	0.3MIN.
e	0.8
b	0.50±0.05
x	0.08
y	0.1
y1	0.2
SE	1.20
ZD	1.915
ZE	1.78

* : It applies to hatching part.