


JEITA Package code	RENESAS code	Previous code	MASS(TYP.)[g]
P-TFBGA36-4x4-0.50	PTBG0036KA-A	P36F1-50-AA6	0.027



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	3.90	4.00	4.10
E	3.90	4.00	4.10
A	—	—	1.10
A ₁	0.17	0.22	0.27
e	—	0.50	—
b	0.26	0.31	0.36
x	—	—	0.05
y	—	—	0.08
y ₁	—	—	0.20
Z _D	—	0.75	—
Z _E	—	0.75	—
w	—	—	0.20