

外形図 Outline drawing




Renesasコード PTLG0145JC-A

RDK-G-001621

1/1

ルネサスエレクトロニクス株式会社
Renesas Electronics Corporation

| | | |
|---------------------|--------------|---------------|
| JEITA Package code | RENESAS code | MASS(TYP.)[g] |
| P-TFLGA145-9×9-0.65 | PTLG0145JC-A | 0.16 |



| Reference Symbol | Dimension in Millimeters | | |
|------------------|--------------------------|------|------|
| | Min. | Nom. | Max. |
| D | — | 9.00 | — |
| E | — | 9.00 | — |
| D1 | — | 7.80 | — |
| E1 | — | 7.80 | — |
| A | — | — | 1.01 |
| b | — | 0.35 | — |
| e | — | 0.65 | — |
| aaa | — | — | 0.10 |
| ccc | — | — | 0.10 |
| ddd | — | — | 0.10 |
| eee | — | — | 0.08 |
| fff | — | — | 0.08 |
| n | — | 145 | — |