




# 80-PIN PLASTIC FLGA (7.5x7.5)




Detail of (A) part



Detail of (B) part



Detail of (C) part



ITEM	MILLIMETERS
D	7.50±0.10
E	7.50±0.10
w	0.20
e	0.65
A	1.13±0.07
b	0.35±0.05
x	0.08
y	0.10
y1	0.20
ZD	1.15
ZE	1.15