




JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-TFQFP100-14x14-0.50	PTQP0100KB-D	TFP-100JV	0.5g




Terminal cross section
(Ni/Pd/Au plating)



Detail F

NOTE)
1. DIMENSIONS**1**AND**2**
DO NOT INCLUDE MOLD FLASH
2. DIMENSION**3**DOES NOT
INCLUDE TRIM OFFSET.



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14.0	—
E	—	14.0	—
A ₂	—	1.0	—
H _D	15.7	16.0	16.3
H _E	15.7	16.0	16.3
A	—	—	1.20
A ₁	0.00	0.10	0.20
b _p	0.15	0.20	0.25
b ₁	—	—	—
c	0.10	0.15	0.20
c ₁	—	—	—
θ	0°	—	8°
e	—	0.5	—
x	—	—	0.08
y	—	—	0.10
Z _D	—	1.00	—
Z _E	—	1.00	—
L	0.4	0.5	0.6
L ₁	—	1.00	—