

JEITA Package Code

RENESAS Code

Previous Code



MASS[Typ.]

P-TFQFP80-12x12-0.50


PTQP0080KC-A

TFP-80C/TFP-80CV

0.4g




Terminal cross section



Detail F

NOTE)

1. DIMENSIONS *1* AND *2* DO NOT INCLUDE MOLD FLASH
2. DIMENSION *3* DOES NOT INCLUDE TRIM OFFSET.



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	12	—
E	—	12	—
A ₂	—	1.00	—
H _D	13.8	14.0	14.2
H _E	13.8	14.0	14.2
A	—	—	1.20
A ₁	0.00	0.10	0.20
b _p	0.17	0.22	0.27
b ₁	—	0.20	—
c	0.12	0.17	0.22
c ₁	—	0.15	—
θ	0°	—	8°
e	—	0.5	—
x	—	—	0.10
y	—	—	0.10
Z _D	—	1.25	—
Z _E	—	1.25	—
L	0.4	0.5	0.6
L ₁	—	1.0	—