





JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
P-TSOP(2)44-10.16x18.41-0.80	PTSB0044GD-B	44P3F-B	0.4g



- NOTE)
1. DIMENSIONS $*1$ AND $*2$ DO NOT INCLUDE MOLD FLASH.
 2. DIMENSION $*3$ DOES NOT INCLUDE TRIM OFFSET.



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	18.31	18.41	18.51
E	10.06	10.16	10.26
A_2	—	1.0	—
A_1	0.05	0.125	0.2
A	—	—	1.2
b_p	0.3	0.35	0.45
c	0.105	0.125	0.175
θ	0°	—	10°
H_E	11.56	11.76	11.96
[e]	—	0.8	—
x	—	—	0.16
y	—	—	0.10
Z	—	0.805	—
Z_1	—	—	0.955
L	0.4	0.5	0.6
L_1	—	0.8	—